

Bracket Pro Serie 40™

Mounting system for Monitor / Defibrillator Philips MRx

Characteristics

- Lightweight
- Compact size
- Swivel base 360° **with locking system**
- Quick Release and re-attachment
- Safe and Easy
- immediate access
- Match with other mount system from us.
- **SAE 3043 certified**

Application of use

- Crash cart
- Ambulance
- EMS Vehicles
- Helicopter
- Aircraft
- Stretcher/cot
- Military Vehicles

Advantages

- Minimum space for installation
- No vertical release
- Latex free
- Resist to the biological fluid
- Insensitive to rust
- 1 year full warranty

Any medical equipment that has been inadequately installed in ambulances, helicopters and other emergency medical service vehicles (EMS) and crash carts, can potentially pose a serious risk or become dangerous in the event that the vehicle makes frequent or sudden stops, turns or rushed departures. This situation can result in damaged expensive medical equipment or even inflict injuries on a patient, ambulance personnel or clinic staff.



Our locking systems "**Bracket Pro Serie 40™**" are designed for fast access to the unit, with little effort in times of emergency uses. The features of this support are the very small size (weight) and the method of locking it (*no vertical movement; less potential injury overtime, and minimum space for installation*).

To spare the expenses of costly repair or replacement of the equipment, and medical care and possible legal redress for injury, consider outfitting your EMS vehicle or crash cart with a deployment system for monitor and/or defibrillator.

The mounting systems offer different configurations for most external defibrillators on the market. They have many characteristics, more specifically to rotate up to 360 degrees with a locking system. The deployment of the unit is almost instantaneously and the system locked the unit after use and resist to an impact of many times the «G» Force.

Technimount System Inc sells, develops, and commercialize deployment system for medical equipment that can be fit with different brand names of defibrillator, in hospital, EMS, or military environment.



For use with model [Philips](#) Defibrillator « [MRx™](#) »

TECHNICAL SPECIFICATIONS¹

Product name:	Bracket Pro Serie 40
Compatibility model:	Monitor – Defibrillator Philips « <i>MRx</i> »
Environment of use:	EMS / Hospital – Clinic – Biomed shop – Military hospital -
Material:	Base: Aluminum high density w/ anodize process Roll Cage: Soft steel with heated coat - black
Temperature of use:	- 35° C @ 45° C (Direct conduction)
Impact Resistance²:	(30«G») Plus 10% safety factor (<i>On certified hook</i>)
Nbr of installation point:	4 points on surface base: 6 points on device mount
Dimensions (both parts assy- overall):	11-1/4" Width X 9-3/4" Depth X 13-1/4" Height (inch.)
Rotation:	360° degrees with locking system (small base) 15° degrees both sides with locking system (Long base)
Features:	- Compatible with Technimount cot system - Compatible with Extended surface base - Free access to all connectors
Weight:	Total (2 parts) 3.9 lbs - device section: 1.80 lbs. –
Option:	Hospital Version (No Carry case) EMS Version (With Carry case) Extended surface base (longer) Spacer (extension mount 3/8", 1/2", 3/4") Table top converter (surface base cover for work space)
Locking mechanism resistance:	Over than 20 000 movements without any fatigue
Features:	With Carry case protector
Part number¹:	300-00-PH Complete NO carry case
Part number¹:	300-00-PHBG Complete WITH bag
Part number¹:	300-10-PH Roll cage & disc only upper part NO bag
	300-10-PHBG Roll cage & disc only upper part With bag
Part number¹:	100-20-UN Surface base part only (small - standard)



Installation suggested

¹ Part number must be confirmed prior sending purchase order. Technimount System inc reserves the right to make changes on the product, documents and technical specifications without notice and responsibilities. DOCUMENTS PRINTED IN CANADA
CGC Technologies – Division of Medical equipment & accessories – Registered brand 2013

² *Technimount System Inc* works to meet and exceed all legal requirements in the deployment system for EMS vehicles, according to the Provincial & Federal Government regulations, it may not meet your local requirements, please contact your administrator.